



# Mobile hand wash station

## HGP230 Hygienius ProWash

The preprogrammed wash cycle is designed to match the World Health Organization Guidelines *"Clean hands protect against infection"* - resulting in highly efficient water usage.

Designed for medical and healthcare settings

Handwash stations must "...be used for that purpose only" - National infection prevention and control manual for England

The Hygienius ProWash can be plugged in to any convenient 13 amp socket

 Order online at [tealwash.com](http://tealwash.com)

The Hygienius ProWash mobile handwash station is entirely self contained and needs no mains water service or drainage connections.

# Featuring a preprogrammed hand wash/rinse cycle

To start the timed wash programme:-

1. Place your hands in the bowl by the sensor and the automatic sensor will start to flash, beginning the wash/rinse cycle. Water will be dispensed for 3 seconds to enable hands to be wetted.
2. Apply soap and lather thoroughly for a period of 20 seconds. At the end of that time, warm water will be dispensed for 10 seconds to enable soap to be washed off the hands.
3. Remove hands from the bowl and dry with a paper towel. The Hygienius ProWash will automatically reset ready for the next user.
4. The total wash time is approximately 35 seconds.

Features of the Hygienius ProWash:-

- Hands free operation under warm running water.
- The water always at the optimum temperature of 38° - 40°C.
- Highly portable - the Hygienius ProWash mobile handwash station can be plugged in to any convenient 13 amp socket.
- Nothing to reset or adjust - simple daily hygiene routine.
- Highly efficient use of water - up to 40 wet/soap/rinse cycles per filling of the TEALTainer water container.
- The TEALTainer ensures that fresh and waste water are kept separate and hygienically contained.
- A soap dispenser and paper towel holder are included.

Specification

- Overall height 990mm
- Height to bowl 900mm
- Width 330mm
- Weight (dry) 7.6kg
- Power supply 230V mains

Construction

- The body is fully moulded in blue fleck high impact polyethylene.
- The bowl is white acrylic capped ABS.
- Comes complete with 13 amp moulded plug.
- TEALTainer II securely retains waste water in a separate heavy duty LLDPE polythene 9 litre bag.

Included with the ProWash

- TEALTainer II water container.
- Stainless steel paper towel holder.
- "Z" bracket for soap dispenser.



 Order online  
at [tealwash.com](http://tealwash.com)

Handwash stations must "...be used for that purpose only" - National infection prevention and control manual for England



**Teal Patents Ltd**

Unit 2  
Chelmsley Wood Industrial Estate  
Waterloo Avenue  
Chelmsley Wood  
Birmingham, B37 6QQ, UK  
Tel: +44 (0) 121 770 0593  
Email: [enquiries@tealwash.com](mailto:enquiries@tealwash.com)

Order online at [www.tealwash.com](http://www.tealwash.com)

